Product datasheet

Specification





PC box IP66 IK08 RAL7035 Int.H105W105D55 Ext.H116W116D62 opaque PC cover H10

Local distributor code: 387531690

NSYTBP11116

EAN Code: 3606480165610

Main

Range	Thalassa	
Product Name	Thalassa TBP	
Device Application	olication Multi-purpose	
Category	Industrial box	
Height	116 mm	
Width	116 mm	
Depth	h 62 mm	
Internal Height	al Height 105 mm	
Internal Width	ernal Width 105 mm	
nternal Depth 55 mm		
Enclosure Mounting	Wall mounted	
Device Composition	1 body 1 cover 4 cover screw	
Quantity Per Set	Set of 5	
Body Type	One piece moulded	
Type Of Front Cover	Low plain cover	
Cover Fixing	Plastic screws	
Lock Type	Captive screw flat outside sealed area	
Removable Parts	Cover by captive screws	

Complementary

Material	Polycarbonate	
Colour	Grey (RAL 7035)	
Standards	IEC 62208 UL 508 A	
Product Certifications	TÜV UL	
Electrical Insulation Class	Class II	
Mounting Location	Outdoor (with canopy or shelter and anticondensation valve)	
Net Weight	0.171 kg	

Environment

Ip Degree Of Protection	IP66 conforming to NEMA 4.4X
Ik Degree Of Protection	IK08 conforming to IEC 62262
Fire Resistance	960 °C
Ambient Air Temperature For Storage	-1560 °C
Operating Temperature	-2580 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.2 cm
Package 1 Width	12.0 cm
Package 1 Length	33.0 cm
Package 1 Weight	171.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	12.2 cm
Package 2 Width	12.0 cm
Package 2 Length	33.0 cm
Package 2 Weight	857.0 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	75
Package 3 Height	40.0 cm
Package 3 Width	40.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	14.66 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information