# **Product datasheet**

Specification





### PC box IP66 IK08 RAL7035 Int.H125W80D65 Ext.H138W93D72 Transp.cover H20

Local distributor code:

387531920

NSYTBP1397T

EAN Code: 3606480165788

#### Main

Range	Thalassa	
Product Name	Thalassa TBP	
Device Application	Multi-purpose	
Category	Industrial box	
Height	138 mm	
Width	93 mm	
Depth	pth 72 mm	
Internal Height	rnal Height 125 mm	
nternal Width 80 mm		
Internal Depth	65 mm	
Enclosure Mounting	Wall mounted	
Device Composition	1 body 1 cover 4 cover screw	
Quantity Per Set	Set of 2	
Body Type	One piece moulded	
Type Of Front Cover	Low transparent cover	
Cover Fixing	Plastic screws	
Lock Type	Captive screw flat outside sealed area	
Removable Parts	Cover by captive screws	

### Complementary

Material	Polycarbonate	
Colour	Grey (RAL 7035) Transparent	
Standards	IEC 62208 UL 508 A	
Product Certifications	TÜV UL	
Electrical Insulation Class	Class II	
Mounting Location	ion Outdoor (with canopy or shelter and anticondensation valve)	
Net Weight	0.23 kg	

#### **Environment**

Ip Degree Of Protection	IP66 conforming to NEMA 4.4X
Ik Degree Of Protection	IK08 conforming to IEC 62262
Fire Resistance	960 °C
Ambient Air Temperature For Storage	-1560 °C
Operating Temperature	-2580 °C

# **Packing Units**

<b>J</b>	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	9.3 cm
Package 1 Length	13.8 cm
Package 1 Weight	230 g
Unit Type Of Package 2	PAM
Number Of Units In Package 2	1160
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	173 cm
Package 2 Weight	404 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information