Product datasheet

Specifications





PC box IP66 IK08 RAL7035 Int.H225W175D80 Ext.H241W194D194 opaque PC cover H20

Local distributor code: 387531784

NSYTBP24198

EAN Code: 3606480165689

IVI	aı	n

Range	Thalassa
Product Name	Thalassa TBP
Device Application	Multi-purpose
Category	Industrial box
Height	241 mm
Width	194 mm
Depth	87 mm
Internal Height	225 mm
Internal Width	175 mm
Internal Depth	80 mm
Enclosure Mounting	Wall mounted
Device Composition	1 body 1 cover 4 cover screw
Body Type	One piece moulded
Type Of Front Cover	Low plain cover
Cover Fixing	Plastic screws
Lock Type	Captive screw flat outside sealed area
Removable Parts	Cover by captive screws

Complementary

Material	Polycarbonate
Colour	Grey (RAL 7035)
Standards	UL 508 A IEC 62208
Product Certifications	TÜV UL
Electrical Insulation Class	Class II
Mounting Location	Outdoor (with canopy or shelter and anticondensation valve)
Net Weight	0.64 kg

Environment

Ip Degree Of Protection

IP66 conforming to NEMA 4.4X

Ik Degree Of Protection	IK08 conforming to IEC 62262
Fire Resistance	960 °C
Ambient Air Temperature For Storage	-1560 °C
Operating Temperature	-2580 °C

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	20.0 cm
Package 1 Length	25.5 cm
Package 1 Weight	699.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	12
Package 2 Height	40.5 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	9.6 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	144
Package 3 Height	120 cm
Package 3 Width	80 cm
Package 3 Length	136 cm
Package 3 Weight	128 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information