Product datasheet

Specification





PC box IP66 IK08 RAL7035 Int.H225W175D80 Ext.H241W194D87 Transp.cover H20

Local distributor code:

387531991 NSYTBP24198T

EAN Code: 3606480165849

Main

Range	Thalassa	
Product Name	Thalassa TBP	
Device Application	Multi-purpose	
Category	Industrial box	
Height	241 mm	
Width	194 mm	
Depth	oth 87 mm	
Internal Height	rnal Height 225 mm	
Internal Width	175 mm	
Internal Depth	80 mm	
Enclosure Mounting	Wall mounted	
Device Composition	1 body 1 cover 4 cover screw	
Body Type	One piece moulded	
Type Of Front Cover	Low transparent cover	
Cover Fixing	Plastic screws	
Lock Type	Captive screw flat outside sealed area	
Removable Parts	Cover by captive screws	

Complementary

Material	Polycarbonate	
Colour	Grey (RAL 7035) Transparent	
Standards	UL 508 A IEC 62208	
Product Certifications	TÜV UL	
Electrical Insulation Class	Class II	
Mounting Location	Outdoor (with canopy or shelter and anticondensation valve)	
Net Weight	0.64 kg	

Environment

Ip Degree Of Protection IP66 conforming to NEMA 4.4X

Ik Degree Of Protection	IK08 conforming to IEC 62262
Fire Resistance	960 °C
Ambient Air Temperature For Storage	-1560 °C
Operating Temperature	-2580 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	20.0 cm
Package 1 Length	25.5 cm
Package 1 Weight	698.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	12
Package 2 Height	40.5 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	9.78 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	300
Package 3 Height	220.0 cm
Package 3 Width	100.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	258.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information