Product datasheet

Specification





ABS box IP66 IK07 RAL7035 Int.H175W150D80 Ext.H193W164D87 Opaque cover H20

Local distributor code:

387531218

NSYTBS19168

EAN Code: 3606480165306

Main

Range	Thalassa	
Product Name	Thalassa TBS	
Device Application	Multi-purpose	
Category	Industrial box	
Height	192 mm	
Width	164 mm	
Depth	87 mm	
Internal Height	175 mm	
Internal Width	150 mm	
Internal Depth	80 mm	
Enclosure Mounting	Wall mounted	
Device Composition	1 body	
	1 cover	
	4 cover screw	
Body Type	One piece moulded	
Type Of Front Cover	Low plain cover	
Cover Fixing	Plastic screws	
Lock Type	Captive screw flat outside sealed area	
Removable Parts	Cover by captive screws	

Complementary

Material	ABS (acrylonitrile butadiene-styrene)	
Colour	Grey (RAL 7035)	
Standards	IEC 62208	
Product Certifications	TÜV	
Electrical Insulation Class	Class II	
Ip Degree Of Protection	IP66 conforming to NEMA 4.4X	
Ik Degree Of Protection	IK07 conforming to IEC 62262	
Glow Wire Resistance	650 °C conforming to IEC 60695-2-11	
Ambient Air Temperature For Storage	-1540 °C	
Operating Temperature	-2560 °C	
Net Weight	0.45 kg	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	17.0 cm
Package 1 Length	20.5 cm
Package 1 Weight	447.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	40.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	9.76 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	240
Package 3 Height	136.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	123.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations