Product datasheet

Specifications





ABS box IP66 IK07 RAL7035 Int.H325W275D160 Ext.H341W291D168 Opaque cover H60

Local distributor code: 387531454

NSYTBS342916H

EAN Code: 3606480165412

Main

Range	Thalassa
Product Name	Thalassa TBS
Device Application	Multi-purpose
Category	Industrial box
Height	341 mm
Width	291 mm
Depth	168 mm
Internal Height	325 mm
Internal Width	275 mm
Internal Depth	160 mm
Enclosure Mounting	Wall mounted
Device Composition	1 body 1 cover 4 cover screw
Body Type	One piece moulded
Type Of Front Cover	High plain cover
Cover Fixing	Plastic screws
Lock Type	Captive screw flat outside sealed area
Removable Parts	Cover by captive screws

Complementary

Material	ABS (acrylonitrile butadiene-styrene)	
Colour	Grey (RAL 7035)	
Standards	IEC 62208	
Product Certifications	TÜV	
Electrical Insulation Class	Class II	
Ip Degree Of Protection	IP66 conforming to NEMA 4.4X	
Ik Degree Of Protection	IK07 conforming to IEC 62262	
Glow Wire Resistance	650 °C conforming to IEC 60695-2-11	
Ambient Air Temperature For Storage	-1540 °C	
Operating Temperature	-2560 °C	
Net Weight	1.66 kg	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	30 cm
Package 1 Length	36 cm
Package 1 Weight	1.63 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	3
Package 2 Height	40 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	5.88 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	36
Package 3 Height	136 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	79 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations