



### Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	336 mm
Height	600 mm
Depth	123 mm
Nb of 18 mm modules per row	13
Nb of horizontal rows	3
Electrical insulation class	Class II Double insulation
Provided equipment	2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip

### Complementary

Enclosure mounting	Surface
9 mm pitches	26
Total number of 18 mm modules	39
Power dissipation in W	45 W
[In] rated current	90 A
Type of rail	DIN
Cable entry	Cut-out plates Cable or tube Removable plates Trunking
Number of terminal blocks	1 earth (Quick) with 22 outgoing 1 neutral (Quick) with 23 outgoing
Distribution block outgoing	2 x 25 mm <sup>2</sup> for earth 20 x 6 mm <sup>2</sup> for earth 3 x 25 mm <sup>2</sup> for neutral 20 x 6 mm <sup>2</sup> for neutral
Enclosure material	Back part: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016)

Front face: grey (RAL 7004)

Targeted country	Finland Russia Sweden Hungary Czech republic Greece Baltic
------------------	--

## Environment

Fire resistance	Back part: 650 °C conforming to IEC 60695-2-1 Front face: 650 °C conforming to IEC 60695-2-1
IP degree of protection	IP30 without door conforming to EN/IEC 60529 IP40 with door conforming to EN/IEC 60529
IK degree of protection	IK08 without door conforming to EN/IEC 62262 IK09 with door conforming to EN/IEC 62262
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">Download RoHS China Declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------