



# Pragma surface enclosure - IP30 - 3 x 13 modules - without door

PRA20313

Local distributor code:

391268027

Discontinued on: 19 May 2023

! End-of-service on: 31 Oct 2023

(!) Discontinued

EAN Code: 3303432372422

#### Main

Range	Pragma	
Product Or Component Type	Enclosure	
Enclosure Type	Distribution enclosure	
Width	336 mm outside:	
Height	600 mm	
Depth	123 mm	
Nb Of 18 Mm Modules Per Row	13	
Nb Of Horizontal Rows	3	
Electrical Insulation Class	Class II Double insulation	
Provided Equipment	2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip	
Type Of Door	Without	

## Complementary

<b>Enclosure Mounting</b>	Surface
9 Mm Pitches	26
Total Number Of 18 Mm Modules	39
Power Dissipation In W	45 W
[In] Rated Current	90 A
[Ui] Rated Insulation Voltage	400 V
Type Of Rail	DIN
Mounting Plate Description	Without mounting plate
Cable Entry	Cut-out plates Cable or tube Removable plates Trunking
Number Of Terminal Blocks	1 earth (Quick) with 24 outgoers 1 neutral (Quick) with 24 outgoers
Distribution Block Outgoers	3 x 25 mm² for earth 21 x 4 mm² for earth 3 x 25 mm² for neutral 21 x 4 mm² for neutral

Enclosure Material	Back part: technoplastic Front face: technoplastic	
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)	
Targeted Country	Finland Russia Sweden Hungary Czech republic Greece Baltic	
Embedding Depth	0 mm	
Internal Depth	95 mm	

## **Environment**

Fire Resistance	Back part: 650 °C Front face: 650 °C	
Ip Degree Of Protection	IP30 without door IP40 with door	
Ik Degree Of Protection	IK08 without door IK09 with door	
Overvoltage Category	II	
Ambient Air Temperature For Operation	-2560 °C	
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	35.0 cm
Package 1 Length	61.0 cm
Package 1 Weight	4.641 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	21
Package 2 Height	120.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	109.461 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>Ø</b>	Halogen Free Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations