



Main

Range	Acti 9
Product name	IKQ
Product or component type	Residual current circuit breaker
Poles description	2P
[In] rated current	80 A
Network type	AC
Earth-leakage sensitivity	30 mA

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	230 V AC 50/60 Hz
Control type	Toggle
Local signalling	Trip indicator
Mounting mode	Fixed
Mounting support	DIN rail
9 mm pitches	4
Height	81 mm
Width	36 mm
Depth	75 mm
Embedding depth	75 mm
Net weight	0.227 kg
Connections - terminals	Single terminal 50 mm ²

Environment

Standards	BS EN 61008
IP degree of protection	IP20

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------
