



# control station XAL-E with white pushbutton 1C/O + black pushbutton 1C/O

XALE2235

EAN Code: 3389119017879



### Main

Range Of Product	Harmony XALE	
Product Or Component Type	Complete control station	
Device Short Name	XALE	
Product Destination	For XB7 Ø 22 mm control and signalling units	
Control Station Application	Two functions	
Colour Of Base Of Enclosure	Light grey (RAL 7035)	
Colour Of Cover	Light grey (RAL 7035)	
Material	ABS (acrylonitrile butadiene-styrene)	
Ip Degree Of Protection	IP54 conforming to IEC 60529	
Control Station Composition	1 flush push-button, black, spring return, white left arrow marking 1 flush push-button, white, spring return, black right arrow marking	
Marking Location	Marking on push-button	
Contact Operation	Slow-break	

# Complementary

Cable Entry	2 knock-outs, clamping capacity: 20 mm 6 knock-outs for ISO M20	
Net Weight	0.145 kg	
Marking	CE	
Positive Opening	Without	
Short-Circuit Protection	4 A cartridge fuse type gG conforming to EN/IEC 60947-5-1	
[Ui] Rated Insulation Voltage	250 V (pollution degree 3) conforming to EN/IEC 60947-1	
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60947-1	
[le] Rated Operational Current	0.1 A at 250 V, DC-13, R300 conforming to EN/IEC 60947-5-1 0.22 A at 125 V, DC-13, R300 conforming to EN/IEC 60947-5-1 0.3 A at 240 V, AC-14, D300 conforming to EN/IEC 60947-5-1 0.6 A at 120 V, AC-14, D300 conforming to EN/IEC 60947-5-1	
Electrical Reliability	Λ <= 10exp(-6) at 17 V and 5 mA conforming to IEC 60947-5-4	

## **Environment**

Protective Treatment	TC
Ambient Air Temperature For Storage	-4070 °C

Ambient Air Temperature For Operation	-2555 °C  Class II conforming to IEC 60536	
Electrical Shock Protection Class		
Ik Degree Of Protection	IK05 conforming to EN 50102	
Standards	EN/IEC 62208 EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-5	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	7.5 cm
Package 1 Length	14.7 cm
Package 1 Weight	150.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	4
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.103 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

### **XALE2235**

### **Dimensions Drawings**

#### **Dimensions**





- (1) 6 ISO 20 knock-outs.
- (2) 2 knock-outs for cable entry, maximum capacity 20 mm / 0.79 in.
- (3) 2 knock-out elongated fixing holes Ø 3 mm x 5 mm / Ø 0.12 in. x 0.20 in.

Control station XALE fitted with:	c in mm	c in in.
Flush pushbutton	69	2.72
Projecting pushbutton	71	2.79
Illuminated pushbutton	74.5	2.93
Pilot light	71	2.79
Emergency stop without key	89.5	3.52
Selector switch with standard handle	84.5	3.33
Key switch	100	3.94