Product datasheet

Specification





control station with white pushbutton 1NO + black 1NO + red projecting 1NC

Local distributor code:
403022258 XALE3251

EAN Code: 3389119017923

Main

Range Of Product	Harmony XALE	
Product Or Component Type	Complete control station	
Device Short Name	XALE	
Product Destination	For XB7 Ø 22 mm control and signalling units	
Control Station Application	Three functions	
Colour Of Base Of Enclosure	Light grey (RAL 7035)	
Colour Of Cover	Light grey (RAL 7035)	
Material	ABS (acrylonitrile butadiene-styrene)	
Ip Degree Of Protection	IP54 conforming to IEC 60529	
Control Station Composition	1 flush push-button, black, spring return 1 NO, white down arrow marking 1 flush push-button, white, spring return 1 NO, black up arrow marking 1 projecting push-button, red, spring return 1 NC, white O marking	
Marking Location	Marking on push-button	
Contact Operation	Slow-break	

Complementary

Cable Entry	2 knock-outs, clamping capacity: 20 mm 6 knock-outs for ISO M20	
Net Weight	0.17 kg	
Marking	CE	
Positive Opening	With conforming to EN/IEC 60947-5-1 appendix K	
Short-Circuit Protection	4 A cartridge fuse type gG conforming to EN/IEC 60947-5-1	
[Ui] Rated Insulation Voltage	250 V (pollution degree 3) conforming to EN/IEC 60947-1	
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60947-1	
[le] Rated Operational Current	0.1 A at 250 V, DC-13, R300 conforming to EN/IEC 60947-5-1 0.22 A at 125 V, DC-13, R300 conforming to EN/IEC 60947-5-1 0.3 A at 240 V, AC-14, D300 conforming to EN/IEC 60947-5-1 0.6 A at 120 V, AC-14, D300 conforming to EN/IEC 60947-5-1	
Electrical Reliability	Λ <= 10exp(-6) at 17 V and 5 mA conforming to IEC 60947-5-4	

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2555 °C

Electrical Shock Protection Class	Class II conforming to IEC 60536	
Ik Degree Of Protection	IK05 conforming to EN 50102	
Standards	EN/IEC 60947-5-5 EN/IEC 60947-5-1 EN/IEC 62208 EN/IEC 60947-1	

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.8 cm
Package 1 Width	10.2 cm
Package 1 Length	15 cm
Package 1 Weight	175 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	20
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.017 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards


Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	

XALE3251

Dimensions Drawings

Dimensions

mm in.



- (1) 6 ISO 20 knock-outs.
- (2) 2 knock-outs for cable entry, maximum capacity 20 mm / 0.79 in.
- (3) 2 knock-out elongated fixing holes Ø 3 mm x 5 mm / Ø 0.12 in. x 0.20 in.

Control station XALE fitted with:	c in mm	c in in.
Flush pushbutton	69	2.72
Projecting pushbutton	71	2.79
Illuminated pushbutton	74.5	2.93
Pilot light	71	2.79
Emergency stop without key	89.5	3.52
Selector switch with standard handle	84.5	3.33
Key switch	100	3.94