# **Product datasheet**

Specification





# control station with white pb 1NO + black pb 1NO + selector switch 1 NO

Local distributor code: 403022436

03022436 XALE3441

EAN Code: 3389119017978

### Main

Range Of Product	Harmony XALE
Product Or Component Type	Complete control station
Device Short Name	XALE
Product Destination	For XB7 Ø 22 mm control and signalling units
Control Station Application	Three functions
Colour Of Base Of Enclosure	Light grey (RAL 7035)
Colour Of Cover	Light grey (RAL 7035)
Material	ABS (acrylonitrile butadiene-styrene)
Ip Degree Of Protection	IP54 conforming to IEC 60529
Control Station Composition	1 flush push-button, black, spring return 1 NO, white down arrow marking 1 flush push-button, white, spring return 1 NO, black up arrow marking 1 key selector switch, stay put 1 NO, white O-I marking
Marking Location	Marking on push-button Marking on legend holder
Contact Operation	Slow-break

## Complementary

Cable Entry	2 knock-outs, clamping capacity: 20 mm 6 knock-outs for ISO M20	
Net Weight	0.18 kg	
Marking	CE	
Operator Position Information	2 positions	
Key Number	455	
Key Withdrawal Position	Left-hand	
Positive Opening	Without	
Short-Circuit Protection	4 A cartridge fuse type gG conforming to IEC 60947-5-1	
[Ui] Rated Insulation Voltage	250 V (pollution degree 3) conforming to IEC 60947-1	
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1	
[le] Rated Operational Current	0.1 A at 250 V, DC-13, R300 conforming to IEC 60947-5-1 0.22 A at 125 V, DC-13, R300 conforming to IEC 60947-5-1 0.3 A at 240 V, AC-14, D300 conforming to IEC 60947-5-1 0.6 A at 120 V, AC-14, D300 conforming to IEC 60947-5-1	
Electrical Reliability	Λ <= 10exp(-6) at 17 V and 5 mA conforming to IEC 60947-5-4	

## **Environment**

Protective Treatment	TC
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2555 °C
Electrical Shock Protection Class	Class II conforming to IEC 60536
Ik Degree Of Protection	IK05 conforming to IEC 62262
Standards	IEC 62208 IEC 60947-5-1 IEC 60947-1 IEC 60947-5-5

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	7.5 cm
Package 1 Length	14.7 cm
Package 1 Weight	206.5 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	20
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.893 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	400
Package 3 Height	111.5 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	102.6 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>Ø</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**


Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	

## **XALE3441**

#### **Dimensions Drawings**

#### **Dimensions**

mm in.



- (1) 6 ISO 20 knock-outs.
- (2) 2 knock-outs for cable entry, maximum capacity 20 mm / 0.79 in.
- (3) 2 knock-out elongated fixing holes Ø 3 mm x 5 mm / Ø 0.12 in. x 0.20 in.

Control station XALE fitted with:	c in mm	c in in.
Flush pushbutton	69	2.72
Projecting pushbutton	71	2.79
Illuminated pushbutton	74.5	2.93
Pilot light	71	2.79
Emergency stop without key	89.5	3.52
Selector switch with standard handle	84.5	3.33
Key switch	100	3.94