Product datasheet

Specification





yellow empty enclosure lid with light grey base - 3 cut-outs Local distributor code:

Local distributor code: 393523087

XALK03

EAN Code: 3389110127324

Main

Range Of Product	Harmony XALK	
Product Or Component Type	Empty control station	
Device Short Name	XALK	
Product Destination	For XB5 Ø 22 mm control and signalling units	
Control Station Application	Emergency stop function Emergency switching off function	
Number Of Cut-Out	3 cut-outs	
Colour Of Base Of Enclosure	Light grey (RAL 7035)	
Colour Of Cover	Yellow (RAL 1021)	
Material	Polycarbonate	
Cable Entry	2 knock-outs for cable entry, clamping capacity: 14 mm 2 knock-outs for Pg 13 cable gland and ISO M20, clamping capacity: 12 mm	
Ip Degree Of Protection	IP66 conforming to IEC 60529 IP67 IP69 IP69K	

Complementary

Assembly Style	For customer assembly	
Number Of Horizontal Rows	1	
Number Of Vertical Rows	3	
Net Weight	0.238 kg	
Resistance To High Pressure Washer	7000000 Pa at 55 °C, distance : 0.1 m	
Mounting Of Block	Front mounting Rear mounting	
Main Group	3 cut-outs	
Group Of Product	Standard vellow	

Environment

Protective Treatment	TH
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-4070 °C
Overvoltage Category	Class II conforming to IEC 60536
Nema Degree Of Protection	NEMA 13 NEMA 4X

Ik Degree Of Protection IK03 conforming to EN 50102	
Standards	JIS C8201-5-1
	EN/IEC 60947-5-1
	CSA C22.2 No 14
	UL 508
	EN/IEC 60947-1
	EN/IEC 60947-5-4
	EN/IEC 60947-5-5
	JIS C8201-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7.0 cm
Package 1 Length	13.7 cm
Package 1 Weight	226.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	30
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.277 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

XALK03

Dimensions Drawings

Dimensions



- (1) 2 knock-outs for Pg 13.5 cable gland, maximum capacity 12 mm/0.47 in. (2) Knock-out for cable entry, maximum capacity 14 mm/0.55 in.

Control station fitted with:	c in mm	c in in.
Flush pushbutton	62	2.44
Illuminated pushbutton	64	2.52
Pilot light	65.5	2.58
Projecting pushbutton	66	2.60
Selector switch	80	3.15
Key switch	105.5	4.15