Product datasheet

Specifications





drilled front plate - XAP-E - metal - 3 horizontal openings

Local distributor code: 21152458

XAPE303

EAN Code: 3389110628043

Main

Range Of Product	Harmony XAP				
Product Or Component Type	Front plate with fixing screws				
Device Short Name	XAPE				
Product Destination	For Ø 22 mm control and signalling units				
Product Front Plate Size	72 x 138 mm				
Number Of Cut-Out	3 cut-outs				
Material	Anodised aluminium				
Device Mounting	Flush				
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP657 conforming to NF C 20-010				
Resistance To Chemical Agents	Good resistant to acetone Good resistant to alcohols Good resistant to chloride and fluoride solvents Good resistant to diluted mineral acids Good resistant to oils and petrol Good resistant to organic acids Good resistant to salts				

Complementary

Net Weight	0.095 kg
Environment	
Protective Treatment	TC TH
Ambient Air Temperature For Storage	-4070 °C

eterage	
Ambient Air Temperature For Operation	-2570 °C
Overvoltage Category	Class I conforming to IEC 60536 Class I conforming to NF C 20-030

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	1.500 cm
Package 1 Length	14.200 cm
Package 1 Weight	114.000 g

Unit Type Of Package 2	S02
Number Of Units In Package 2	30
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.790 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards


Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Circularity Profile	No need of specific recycling operations		

Product datasheet


Dimensions Drawings

Dimensions and Fixing

Below drawing shows a front plate with 4 cut-outs. Refer to the product characteristics to get the number of cut-outs.







b		b1		Н	
mm	in.	mm	in.	mm	in.
138	5.43	110	4.33	122	4.80