## **Product datasheet**

Specifications





# drilled front plate - XAP-E - metal - 5 horizontal openings

Local distributor code: 388805875

XAPE305

EAN Code: 3389110628081

#### Main

Range Of Product	Harmony XAP	
Product Or Component Type	Front plate with fixing screws	
Device Short Name	XAPE	
Product Destination	For Ø 22 mm control and signalling units	
Product Front Plate Size	72 x 204 mm	
Number Of Cut-Out	5 cut-outs	
Material	Anodised aluminium	
Device Mounting	Flush	
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP657 conforming to NF C 20-010	
Resistance To Chemical Agents	Good resistant to acetone Good resistant to alcohols Good resistant to chloride and fluoride solvents Good resistant to diluted mineral acids Good resistant to oils and petrol Good resistant to organic acids Good resistant to salts	

### Complementary

Net Weight	0.135 kg		
Environment			
Protective Treatment	TH		
	TC		

	тс
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2570 °C
Overvoltage Category	Class I conforming to IEC 60536 Class I conforming to NF C 20-030

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	13.9 cm
Package 1 Length	23.0 cm
Package 1 Weight	160.0 g

Unit Type Of Package 2	S02
Number Of Units In Package 2	21
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.669 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

## **Product datasheet**


#### **Dimensions Drawings**

#### **Dimensions and Fixing**

Below drawing shows a front plate with 4 cut-outs. Refer to the product characteristics to get the number of cut-outs.







b		b1		Н	
mm	in.	mm	in.	mm	in.
204	8.03	176	6.93	188	7.40