



## empty control station - XAP-M metal - without opening

Local distributor code: 393523210

XAPM44

! Discontinued on: 2 Feb 2023

EAN Code: 3389110312720

### Main

Range Of Product	Harmony XAP					
Product Or Component Type	Die-cast empty control station					
Device Short Name	ХАРМ					
Product Front Plate Size	80 x 220 mm					
Usable Depth	74.5 mm					
Number Of Cut-Out	Undrilled					
Colour Of Base Of Enclosure	Blue					
Colour Of Cover	Blue					
Material	Zinc alloy					
Cable Entry	1 hole without blanking plug for cable gland, clamping capacity: 18 mm					
Product Mounting	Flush mounting					
Ip Degree Of Protection	IP65 conforming to IEC 60529					

#### **Complementary**

**Net Weight** 1.41 kg

### **Environment**

Protective Treatment	TC				
Ambient Air Temperature For Storage	-4070 °C				
Ambient Air Temperature For Operation	-4070 °C				
Electrical Shock Protection Class	Class I conforming to IEC 60536 Class I conforming to NF C 20-030				

### **Packing Units**

20 May 2024

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.8 cm
Package 1 Width	13 cm
Package 1 Length	23.2 cm
Package 1 Weight	1.595 kg

# **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance


<b>②</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

### **Dimensions Drawings**

#### **Dimensions and Fixing**



- (1) 1 hole, without blanking plug, for cable gland with 18 mm/0.71 in. maximum clamping capacity
- (3)  $2 \times \emptyset$  5.6 mm/0.22 in. holes, depth 20 mm/0.79 in.

а		b		С		G		Н		Р	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	220	8.66	77	3.03	50	1.97	205	8.07	74.5	2.93