



INDICATING BEACON 48VDC 10W +OPTIONS

XVBL4B4

Local distributor code: 380657199

EAN Code: 3389110844191

Main

Range Of Product	Harmony XVB Universal	
Product Or Component Type	Complete beacon	
Beacon Or Indicator Bank Unit Type	Base unit direct or tube fixing Illuminated unit	
Signalling Type	Flashing	
Mounting Diameter	70 mm	
Component Name	XVBL	
Material	Glass reinforced polyamide: base unit Polycarbonate: illuminated unit	
Light Source	Bulb not included, red	
Bulb Type	Incandescent Incandescent with BA 15d base Protected LED	
[Us] Rated Supply Voltage	24 V AC 2448 V DC	
Maximum Power Dissipation In W	7 W	

Complementary

Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm² with cable end	
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1	
Nominal Voltage Limit	0.851.1 Un conforming to IEC 60947-5-1	
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1	
Flashing Frequency	1 Hz	
Cad Overall Width	70 mm	
Cad Overall Height	139 mm	
Cad Overall Depth	70 mm	
Terminals Description Iso N°1	(GND)GROUND (COM-1)PW	
Net Weight	0.28 kg	

Environment

Pollution Degree	2	
Product Certifications	CCC	
	EAC	
	CSA C22-2 No 14	
	111 508	

Standards	IEC 60947-5-1	
Protective Treatment	TC	
Ambient Air Temperature For Storage	-4070 °C	
Electrical Shock Protection Class	Class I on support tube conforming to IEC 61140 Class II on base unit conforming to IEC 61140	
Ip Degree Of Protection	IP65 on fixing base XVBZ0. conforming to IEC 60529 IP66 on base unit conforming to IEC 60529	
Nema Degree Of Protection	Type 4X conforming to UL (indoor)	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.500 cm
Package 1 Width	8.000 cm
Package 1 Length	8.000 cm
Package 1 Weight	278.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	18
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.480 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

XVBL4B4

Dimensions Drawings

Illuminated Beacon for BA 15d Bulb or LED

Dimensions



Product datasheet

XVBL4B4

Connections and Schema

Illuminated Beacon

Wiring Diagram

