# **Product datasheet**

Specifications





① Discontinued

## LED pilot light with black bezel, Harmony XVL, Ø 8, IP40, yellow, protruding included, 5 V, faston

XVLA115

() Discontinued on: 31 Mar 2023

(!) End-of-service on: 15 Apr 2023

#### EAN Code: 3389110650983

### Main

Range Of Product	Harmony XVL		
Product Or Component Type	LED pilot light with black bezel		
Component Name	XVL		
Mounting Diameter	8 mm		
Light Source	Protruding LED		
Light Block Colour	Yellow		
Protection Type	Built-in by diode Integral ballast resistor		
[Us] Rated Supply Voltage	5 V		
Ip Degree Of Protection	IP40 conforming to IEC 60529 IP40 conforming to NF C 20-010		

### Complementary

Supply Circuit Type	DC	
Connections - Terminals	Tag for Faston connectors: 2.8 x 0.5 mm Tag for soldering connectors	
Current Consumption	25 mA	
[Ui] Rated Insulation Voltage	50 V conforming to IEC 60947-1	
Bulb Lifespan	100000 h	
Nominal Voltage Limit	0.81.1 Un	
Terminals Description Iso N°1	(X1-X2)PL	
Height	12 mm	
Width	12 mm	
Depth	34 mm	
Net Weight	0.003 kg	

### Environment

Product Certifications	CSA UL
Protective Treatment	тс
Ambient Air Temperature For Operation	-2570 °C

Ambient Air Temperature For Storage	-4070 °C
Overvoltage Category	Class 3 conforming to IEC 60536 Class 3 conforming to NF C 20-030

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	1.0 cm
Package 1 Length	4.0 cm
Package 1 Weight	3.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	100
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	596.0 g

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free

Rohs Exemption Information
Yes

### **Certifications & Standards**


Circularity Profile	No need of specific recycling operations		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Environmental Disclosure	Product Environmental Profile		
China Rohs Regulation	China RoHS declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
Reach Regulation	REACh Declaration		

## **Product datasheet**

#### **Dimensions Drawings**

#### LED Pilot Light

#### Dimensions



- (1) Tags for Faston connectors or soldered connections
- e panel thickness: 1 to 8 mm/0.03 to 0.31 in.


С		Ø	
mm	in.	mm in.	
32	1.26	12	0.47

## **Product datasheet**

### Mounting and Clearance

#### LED Pilot Light

#### Panel Drilling



Ø min		G min		H min	
mm	in.	mm	in.	mm	in.
8.2	0.32	12.5	0.49	12.5	0.49