# **Product datasheet**

Specifications





# pilot light Ø8 - IP40 - red protruding LED included - 24V -

faston

Local distributor code: 385366401

XVLA134

#### EAN Code: 3389110651089

#### Main

Range Of Product	Harmony XVL
Product Or Component Type	LED pilot light with black bezel
Component Name	XVL
Mounting Diameter	8 mm
Light Source	Protruding LED
Light Block Colour	Red
Protection Type	Built-in by diode Integral ballast resistor
[Us] Rated Supply Voltage	24 V
Ip Degree Of Protection	IP40 conforming to IEC 60529 IP40 conforming to NF C 20-010

### Complementary

Supply Circuit Type	DC		
Connections - Terminals	Tag for Faston connectors: 2.8 x 0.5 mm Tag for soldering connectors		
Current Consumption	18 mA		
[Ui] Rated Insulation Voltage	50 V conforming to IEC 60947-1		
Bulb Lifespan	100000 h		
Nominal Voltage Limit	0.81.1 Un		
Terminals Description Iso N°1	(X1-X2)PL		
Height	12 mm		
Width	12 mm		
Depth	34 mm		
Net Weight	0.003 kg		

### Environment

Product Certifications	UL CSA
Protective Treatment	TC
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4070 °C
Overvoltage Category	Class 3 conforming to IEC 60536 Class 3 conforming to NF C 20-030

## **Packing Units**

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.2 cm
Package 1 Width	1.2 cm
Package 1 Length	4.2 cm
Package 1 Weight	3 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3 cm
Package 2 Width	11 cm
Package 2 Length	11 cm
Package 2 Weight	31 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	509 g

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**


Circularity Profile	No need of specific recycling operations		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Environmental Disclosure	Product Environmental Profile		
China Rohs Regulation	China RoHS declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
Reach Regulation	REACh Declaration		

### **Product datasheet**

#### **Dimensions Drawings**

#### LED Pilot Light

#### Dimensions



- (1) Tags for Faston connectors or soldered connections
- e panel thickness: 1 to 8 mm/0.03 to 0.31 in.


С		Ø	
mm	mm in.		in.
32	1.26	12	0.47

### **Product datasheet**

Mounting and Clearance

#### LED Pilot Light

#### Panel Drilling



Ø min		G min		H min	
mm	in.	mm	in.	mm	in.
8.2	0.32	12.5	0.49	12.5	0.49