# **Product datasheet**

Specification





# Illuminated beacon with buzzer, red, Ø100, 70...90 dB, integral LED, 100...230 V AC

Local distributor code: 403036668 XVR3M04S

EAN Code: 3606480611896

#### Main

Range Of Product	Harmony XVR	
Product Or Component Type	Beacon	
Device Short Name	XVR3	
Beacon Or Indicator Bank Unit Type	LED unit	
Sound Signalling	Buzzer: 7090 dB at 1 m	
Mounting Diameter	100 mm	
Light Source	LED, red	
Device Application	Bulldozer Automated guided vehicle (AGV) Forklift	

## Complementary

Signalling Type	Rotating
33	Buzzer
	Blinking
	Flashing
Assembly Style	Ready assembled
Material	PC (polycarbonate): lenses
	PBT (polybutylene terephthalate) + PC (polycarbonate): body
	EPDM (ethylene propylene diene monomer): base
	2. Bill (carylone propylone dione monomer). Base
[Us] Rated Supply Voltage	100230 V AC
[Ue] Rated Operational Voltage	90253 V AC
Inrush Current	0.5 A
Power Consumption In W	3.2 W
Marking	CE
Installation Direction	Upright indoor
	Sideways indoor
	Inverted indoor
	Upright outdoor
	Opright outdoor
Electrical Insulation Class	Class II
Current Consumption	500 mA
Length	100 mm
Width	100 mm
Height	139 mm
Net Weight	0.538 kg

## **Environment**

Product Certifications	CCC	
Ambient Air Temperature For Operation	-1050 °C	
Ambient Air Temperature For Storage	ature For -2070 °C	
Relative Humidity	3585 % without condensation	
Vibration Resistance	4.6 gn (sideways) 4.6 gn (inverted) 4.6 gn (upright)	
Ip Degree Of Protection	IP23 (sideways) IP23 (inverted) IP23 (upright)	

# **Packing Units**

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance


	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

#### **Dimensions Drawings**


#### **Dimensions**




Mounting and Clearance

### Panel Cut-out

#### Straight wiring




#### Side wiring



#### Connections and Schema

#### Wiring Diagram



- (1) Green
- (2) Red
- (3) Yellow
- (4) Black
- (5) White
- (6) LED
- (7) Buzzer
- (8) Com
- (9) Fuse(Rated Current>2A)