# **Product datasheet**

Specifications





# Illuminated beacon with buzzer, orange, Ø100, 70...90 dB, integral LED, 100...230 V AC

Local distributor code: 403036684 XVR3M05S

EAN Code: 3606480611902

#### Main

Range Of Product	Harmony XVR	
Product Or Component Type	Beacon	
Device Short Name	XVR3	
Beacon Or Indicator Bank Unit Type	LED unit	
Sound Signalling	Buzzer: 7090 dB at 1 m	
Mounting Diameter	100 mm	
Light Source	LED, orange	
Device Application	Forklift Bulldozer Automated guided vehicle (AGV)	

## Complementary

Signalling Type	Rotating Blinking Flashing	
Assembly Style	Ready assembled	
Material	PC (polycarbonate): lenses PBT (polybutylene terephthalate) + PC (polycarbonate): body EPDM (ethylene propylene diene monomer): base	
[Us] Rated Supply Voltage	Rated Supply Voltage 100230 V AC	
[Ue] Rated Operational Voltage	90253 V AC	
Inrush Current	sh Current 0.5 A	
Power Consumption In W	3.2 W	
Marking	CE	
Installation Direction	Upright indoor Sideways indoor Inverted indoor Upright outdoor	
Electrical Insulation Class	Class II	
Current Consumption	500 mA	
Length	100 mm	
Width	100 mm	
Height	139 mm	
Net Weight	0.538 kg	

#### **Environment**



Product Certifications	CCC	
Ambient Air Temperature For Operation	-1050 °C	
Ambient Air Temperature For Storage	-2070 °C	
Relative Humidity	3585 % without condensation	
Vibration Resistance	4.6 gn (sideways) 4.6 gn (inverted) 4.6 gn (upright)	
Ip Degree Of Protection	IP23 (sideways) IP23 (inverted) IP23 (upright)	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	13.85 cm
Package 1 Length	18.5 cm
Package 1 Weight	660 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	8
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	29.94 kg
Package 3 Height	30.0 cm

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance


	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

#### **Dimensions Drawings**

#### **Dimensions**




### XVR3M05S


Mounting and Clearance

## Panel Cut-out

#### Straight wiring




#### Side wiring



#### Connections and Schema

#### Wiring Diagram



- (1) Green
- (2) Red
- (3) Yellow
- (4) Black
- (5) White
- (6) LED
- (7) Buzzer
- (8) Com
- (9) Fuse(Rated Current>2A)