

# Product datasheet

Specifications



## Multi-sound Siren 120VDC 2 Tones

Local distributor code:

403036833

XVS10GMW

**EAN Code: 3389119045353**

### Main

Range Of Product	Harmony XVS
Product Or Component Type	Siren
Device Short Name	XVS
Colour	White
Signalling Type	2 tones siren
[Us] Rated Supply Voltage	120 V AC
Noise Level	106 dB (continuous or intermittent tone) at 1 m

### Complementary

Material	PC: body
Net Weight	1 kg
Marking	CE
[Uimp] Rated Impulse Withstand Voltage	4 kV
Current Consumption	80 mA at 120 V
Clamping Connection Capacity	<= 1 x 1.5 mm <sup>2</sup>
Electrical Connection	Cable: 6.5...8.5 mm
Width	114 mm
Height	114 mm
Depth	153.2 mm

### Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-35...70 °C
Ambient Air Temperature For Operation	-30...50 °C
Electrical Shock Protection Class	Class II conforming to EN/IEC 61140
Ip Degree Of Protection	IP53

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	14.0 cm
Package 1 Width	14.0 cm
Package 1 Length	20.0 cm
Package 1 Weight	1.226 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	8
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	11.24 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	32
Package 3 Height	75 cm
Package 3 Width	40 cm
Package 3 Length	80 cm
Package 3 Weight	64.232 kg

### Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-------------------	--

China Rohs Regulation	<a href="#">China RoHS declaration</a>
-----------------------	--

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---

Circularity Profile	<a href="#">End of Life Information</a>
---------------------	---

Dimensions

