



pushbutton head for harsh environment -dark blue-with marking-legend rotated 90°

Local distributor code: 398131911

ZB4BC68006RA

! Discontinued on: 9 Feb 2023



EAN Code: 3606480444708

Main

Range Of Product	Harmony XB4	
Product Or Component Type	Head for push-button	
Device Short Name	ZB4	
Bezel Material	Chromium plated metal	
Head Type	Standard	
Mounting Diameter	22.5 mm	
Sale Per Indivisible Quantity	1	
Cap/Operator Or Lens Colour	Blue	

Complementary

Cad Overall Width	37 mm
Cad Overall Height	18.5 mm
Cad Overall Depth	37 mm
Net Weight	0.036 kg
Electrical Shock Protection Class	Class I conforming to IEC 61140
Shape Of Signaling Unit Head	Round
Type Of Operator	spring return
Operator Profile	Blue flush, type H006 (white)
Operator Additional Information	Horizontal mounting
Mechanical Durability	3000000 cycles
Vibration Resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6
Shock Resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27
Main Group	Harsh environment
Group Of Product	Flush marked type H006
Marking	Type H006
Colour Of Marking	White
Electrical Composition Code	C1 for <9 contacts using single blocks in front mounting C2 for <9 contacts using single and double blocks in front mounting

C11 for <3 contacts using single blocks in front mounting C15 for <1 contacts using single blocks in front mounting

Environment

Ambient Air Temperature For Storage	-4085 °C	
Ambient Air Temperature For Operation	For -4070 °C	
Ip Degree Of Protection	IP66 conforming to IEC 60529 IP69K IP69	
Nema Degree Of Protection	NEMA 4 conforming to UL 508 NEMA 13 NEMA 12	
Resistance To High Pressure Washer	90 Pa at 82.5 °C	
Ik Degree Of Protection	IK06 conforming to IEC 62262	
Standards	UL 508 IEC 60947-5-1 IEC 60947-1 CSA C22.2	
Product Certifications	UL CSA CE	

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	6 cm
Package 1 Length	8 cm
Package 1 Weight	34 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	100
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.652 kg

Contractual warranty

Warranty	18 months	



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

ZB4BC68006RA

Dimensions Drawings

Dimensions




ZB4BC68006RA

Mounting and Clearance


Installation on Flat Surface

Without Protective Guard



(1) Ø22.5 mm recommended (Ø22.3 $_0^{+0.4}$) / Ø0.89 in. recommended (Ø0.88 $_0^{+0.016}$)

With Protective Guard



(1) Ø22.5 mm recommended (Ø22.3 $_0^{+0.4}$) / Ø0.89 in. recommended (Ø0.88 $_0^{+0.016}$)

ZB4BC68006RA

Technical Description

Marking Type H006



Electrical Composition Corresponding to Code C1



Electrical Composition Corresponding to Code C2



ZB4BC68006RA

Electrical Composition Corresponding to Codes C9, C11, SF1 and SR1



Electrical Composition Corresponding to Code C15





1 N/C



1 N/O + N/C or 1 N/O + N/O or 1 N/C + N/C



ZB4BC68006RA

Single contact Double contact Light block Possible location