# Product datasheet

Specifications

## Spacial S3D plain door w/o mount.plate. H1200xW1200xD400 IP55 IK10 RAL7035.

Local distributor code:

392867362 NSYS3D121240D

**EAN Code: 3606480159961**

## Main

| | |
|---|---|
| **Range** | Spacial |
| **Product Name** | Spacial S3D |
| **Application** | Multi-purpose |
| **Category** | Compact enclosure |
| **Enclosure Nominal Height** | 1200 mm |
| **Enclosure Nominal Width** | 1200 mm |
| **Enclosure Nominal Depth** | 400 mm |
| **Door Type** | Plain |
| **Mounting Plate Description** | Without mounting plate |
| **Type Of Gland Plate** | Standard |
| **Installation Accessory Type** | Wall-mounting |
| **Device Composition** | 1 body<br>2 cable gland plate<br>1 lock<br>2 door |

## Complementary

| | |
|---|---|
| **Body Type** | Gutter-shaped front rail double sheet thickness<br>Single piece body |
| **Number Of Doors** | Front face: 2 door(s) |
| **Door Opening Side** | Reversible (120 °) |
| **Lock Type** | 3 points lock, 3 mm double-bar |
| **Accessibility For Operation** | Front |
| **Removable Parts** | Door by hinges<br>Cable gland plate by screws |
| **Material** | Steel |
| **Surface Finish** | Epoxy-polyester powder |
| **Colour** | Grey (RAL 7035) |
| **Standards** | IEC 62208 |
| **Product Certifications** | BV<br>cUL<br>LR<br>DNV<br>GL<br>UL |
| **Net Weight** | 86 kg |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

| | |
|---|---|
| **Electromagnetic Compatibility** | Electromagnetic field immunity test |
| **Ik Degree Of Protection** | IK10 conforming to IEC 62262 |
| **Ip Degree Of Protection** | IP55 conforming to IEC 60529 |

## Packing Units

| | |
|---|---|
| **Unit Type Of Package 1** | PCE |
| **Number Of Units In Package 1** | 1 |
| **Package 1 Height** | 45.0 cm |
| **Package 1 Width** | 122.0 cm |
| **Package 1 Length** | 133.0 cm |
| **Package 1 Weight** | 84.0 kg |

## Contractual warranty

| | |
|---|---|
| **Warranty** | 18 months |

## Sustainability

**Green Premium$^{TM}$ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-$CO_2$ products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >

Transparency

RoHS/REACh

## Well-being performance

| | |
|---|---|
| Mercury Free | |
| Rohs Exemption Information | Yes |

## Certifications & Standards

| | |
|---|---|
| **Reach Regulation** | REACh Declaration |
| **Eu Rohs Directive** | Pro-active compliance (Product out of EU RoHS legal scope) |
| **China Rohs Regulation** | China RoHS declaration<br>Product out of China RoHS scope. Substance declaration for your information |
| **Environmental Disclosure** | Product Environmental Profile |
| **Circularity Profile** | No need of specific recycling operations |