Product datasheet

Specifications

Sreen Premium[™]



(!) Discontinued

SLOTTED MOUNTING PLATE W600 4M

03170

() Discontinued on: 5 Apr 2023

EAN Code: 3606486788882

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Installation Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing enclosure - width 850 mm
Mounting Plate Description	Flat slotted
Number Of Vertical Modules [50 Mm]	4 module(s) in 600 mm Widefloor-standing enclosure 4 module(s) in 600 mm Widewall-mounted enclosure 4 module(s) in 850 mm Widefloor-standing enclosure
Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Surface Finish	Galvanized
Width	600 mm
Height	200 mm
Net Weight	0.72 kg
Functional Unit	600 mm Prisma G floor-standing enclosure 4 12.5 mm 600 mm Prisma G wall-mounted enclosure 4 12.5 mm 850 mm Prisma G floor-standing enclosure 4 12.5 mm

Packing Units

U	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.1 cm
Package 1 Width	19.5 cm
Package 1 Length	46.8 cm
Package 1 Weight	720.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10

Package 2 Height	20.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	7.98 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	120
Package 3 Height	105.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	95.76 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile