
# **Product datasheet**





## FRONT PLATE ISFT100 VERTICAL WIDTH 600/650 6M

03320

! Discontinued on: 9 Aug 2023

EAN Code: 3303430033202

① Discontinued

### Main

Range	Prisma	
Range Of Product	Prisma G Prisma P	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle	
Type Of Front Plate	Cut-out	
Installed Device	FuPact: fixed ISFT100 - control: fuse carriers handle - vertical installation	
Poles Description	5 x 3P: mounting plate support: ISFT100 vertical installation	
Operating Position	Horizontal	

### **Complementary**

Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm	
Connection Position	Direct connection	
Number Of Vertical Modules [50 Mm]	6	
Standards	IEC 61439-2 IEC 61439-1	
Product Certifications	ASEFA	
Material	Steel	
Surface Finish	Matt Smooth	
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder	
Colour	White (RAL 9001)	
Height	300 mm	
Width	500 mm	
Net Weight	1.18 kg	
Quantity Per Set	Set of 1	

Life Is On Schneider 24 Apr 2024

Functional Unit 600 mm Prisma G floor-standing enclosure FuPact ISFT100 fixed fuse carriers

handle vertical 3P 5 direct 7

600 mm Prisma G wall-mounted enclosure FuPact ISFT100 fixed fuse carriers

handle vertical 3P 5 direct 7

 $650~\text{mm}\ 400~\text{mm}$  Prisma P cubicle FuPact ISFT100 fixed fuse carriers handle vertical

3P 5 direct 6

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	31.000 cm
Package 1 Length	51.000 cm
Package 1 Weight	1.171 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	16.500 cm
Package 2 Width	32.000 cm
Package 2 Length	53.000 cm
Package 2 Weight	12.200 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	90
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	121.800 kg

### **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>Ø</b>	Halogen Free Plastic Parts Product

### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile