

Main

Range	Prisma
Range compatibility	Prisma G duct Prisma P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	<p>Compact: fixed NSX400 without earth leakage protection - control: toggle - vertical installation</p> <p>Easypact: fixed CVS400 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Easypact: fixed CVS630 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact: fixed NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact: plug-in NSX400 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact: fixed NSX400 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact: plug-in NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact: plug-in NSX400 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact: fixed NSX630 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact: fixed NSX630 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact: plug-in NSX630 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact: fixed NSX630 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact: plug-in NSX630 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact: plug-in NSX630 without earth leakage protection - control: motor mechanism - vertical installation</p>
Poles description	<p>1 x 4P: mounting plate support: NSX400 vertical installation</p> <p>1 x 3P: mounting plate support: CVS400 vertical installation</p> <p>1 x 4P: mounting plate support: CVS400 vertical installation</p> <p>1 x 3P: mounting plate support: CVS630 vertical installation</p> <p>1 x 4P: mounting plate support: CVS630 vertical installation</p> <p>1 x 3P: mounting plate support: NSX400 vertical installation</p> <p>1 x 3P: mounting plate support: NSX630 vertical installation</p>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

1 x 4P: mounting plate support: NSX630 vertical installation

Operating position	Vertical
--------------------	----------




Complementary

Enclosure/Cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle - width 400 mm depth 400 mm
Connection position	Direct connection Front connection
Number of vertical modules [50 mm]	12
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	600 mm
Width	300 mm
Product weight	1.24 kg
Material	Steel
Surface finish	Smooth Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)

Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------