




Price\* : 117.26 GBP



### Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	Compact : drawout NS630b...1000 - control: direct front rotary handle - vertical installation Compact : drawout NS1250 - control: direct front rotary handle - vertical installation Compact : drawout NS1600 - control: direct front rotary handle - vertical installation Compact : drawout NS630b...1000 - control: motor mechanism - vertical installation Compact : drawout NS1250 - control: motor mechanism - vertical installation Compact : drawout NS1600 - control: motor mechanism - vertical installation Compact : drawout NS630b...1000 - control: toggle - vertical installation Compact : drawout NS1250 - control: toggle - vertical installation Compact : drawout NS1600 - control: toggle - vertical installation Masterpact : drawout NT06...10 - control: toggle - vertical installation Masterpact : drawout NT12 - control: toggle - vertical installation Masterpact : drawout NT16 - control: toggle - vertical installation
Poles description	1 x 3P : drawout : NS630b...1000 vertical installation 1 x 3P : drawout : NS1250 vertical installation 1 x 3P : drawout : NS1600 vertical installation 1 x 3P : drawout : NT06...10 vertical installation 1 x 3P : drawout : NT12 vertical installation 1 x 3P : drawout : NT16 vertical installation

### Complementary

Installation description	Cubicle - width 400 mm, depth 400 mm
Number of vertical modules [50 mm]	36 module(s) : NS1250, direct in 400 mm Wide cubicle 36 module(s) : NS1600, direct in 400 mm Wide cubicle 36 module(s) : NS630b... 1000, direct in 400 mm Wide cubicle 36 module(s) : NT06...10, front connection in 400 mm Wide cubicle 36 module(s) : NT12, front connection in 400 mm Wide cubicle 36 module(s) : NT16, front connection in 400 mm Wide cubicle
Height	30 mm
Product weight	1.62 kg

Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

## Environment

Standards	IEC 61439-2
Product certifications	ASEFA

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available

## Contractual warranty

Warranty period	18 months
-----------------	-----------