


Product datasheet

Specifications



Mounting Plate Vert. Fixed/Withd. MTZ2/NW 3P/4P W650 Prisma P

03500

Discontinued on: 5 Apr 2023

EAN Code: 3303430035008

Discontinued

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Installation Description	Cubicle - width 650 mm depth 600 mm Cubicle - width 650 mm depth 1000 mm
Installed Device	Masterpack: drawout NW08...16 - control: toggle - vertical installation Masterpack: fixed NW08...16 - control: toggle - vertical installation Masterpack: drawout NW20...25 - control: toggle - vertical installation Masterpack: fixed NW20...25 - control: toggle - vertical installation Masterpack: drawout NW32 - control: toggle - vertical installation Masterpack: fixed NW32 - control: toggle - vertical installation
Poles Description	1 x 3P: drawout NW08...16 vertical installation 1 x 3P: fixed NW08...16 vertical installation 1 x 4P: drawout NW08...16 vertical installation 1 x 4P: fixed NW08...16 vertical installation 1 x 3P: drawout NW20...25 vertical installation 1 x 3P: fixed NW20...25 vertical installation 1 x 4P: drawout NW20...25 vertical installation 1 x 4P: fixed NW20...25 vertical installation 1 x 3P: drawout NW32 vertical installation 1 x 3P: fixed NW32 vertical installation 1 x 4P: drawout NW32 vertical installation 1 x 4P: fixed NW32 vertical installation

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Vertical Modules [50 Mm]	36 module(s): NW08...16, front connection on adaptor in 650 mm Widecubicle 27 module(s): NW08...16, front connection on Canalis in 650 mm Widecubicle 15 module(s): NW08...16, rear connection on adaptor in 650 mm Widecubicle 19 module(s): NW08...16, front connection on adaptor in 650 mm Widecubicle 17 module(s): NW08...16, rear connection on Canalis in 650 mm Widecubicle 36 module(s): NW08...16, front connection on busbar in 650 mm Widecubicle 18 module(s): NW08...16, front connection on adaptor in 650 mm Widecubicle 14 module(s): NW08...16, rear connection on adaptor in 650 mm Widecubicle 16 module(s): NW08...16, rear connection on Canalis in 650 mm Widecubicle 36 module(s): NW20...25, front connection on adaptor in 650 mm Widecubicle 15 module(s): NW20...25, rear connection on adaptor in 650 mm Widecubicle 20 module(s): NW20...25, front connection on adaptor in 650 mm Widecubicle 28 module(s): NW20...25, front connection on Canalis in 650 mm Widecubicle 17 module(s): NW20...25, rear connection on Canalis in 650 mm Widecubicle 36 module(s): NW20...25, front connection on busbar in 650 mm Widecubicle 19 module(s): NW20...25, front connection on adaptor in 650 mm Widecubicle 14 module(s): NW20...25, rear connection on adaptor in 650 mm Widecubicle 16 module(s): NW20...25, rear connection on Canalis in 650 mm Widecubicle 36 module(s): NW32, front connection on adaptor in 650 mm Widecubicle 15 module(s): NW32, rear connection on adaptor in 650 mm Widecubicle 20 module(s): NW32, front connection on adaptor in 650 mm Widecubicle 28 module(s): NW32, front connection on Canalis in 650 mm Widecubicle 17 module(s): NW32, rear connection on Canalis in 650 mm Widecubicle 36 module(s): NW32, front connection on busbar in 650 mm Widecubicle 19 module(s): NW32, front connection on adaptor in 650 mm Widecubicle 14 module(s): NW32, rear connection on adaptor in 650 mm Widecubicle 16 module(s): NW32, rear connection on Canalis in 650 mm Widecubicle
Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Colour	White (RAL 9001)
Width	650 mm
Height	30 mm
Net Weight	3.82 kg

650 mm 1000 mm Prisma P cubicle Masterpact NW20...25 fixed toggle vertical 4P 1 rear connection on adaptor 14 437.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW20...25 fixed toggle vertical 4P 1 front connection on Canalis 28 1137.5 mm
650 mm 1000 mm Prisma P cubicle Masterpact NW20...25 fixed toggle vertical 4P 1 rear connection on Canalis 16 787.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW20...25 fixed toggle vertical 4P 1 front connection on busbar 36 1037.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 drawout toggle vertical 3P 1 front connection on adaptor 36 1087.5 mm
650 mm 1000 mm Prisma P cubicle Masterpact NW32 drawout toggle vertical 3P 1 rear connection on adaptor 15 487.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 drawout toggle vertical 3P 1 front connection on adaptor 20 737.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 drawout toggle vertical 3P 1 front connection on Canalis 28 1137.5 mm
650 mm 1000 mm Prisma P cubicle Masterpact NW32 drawout toggle vertical 3P 1 rear connection on Canalis 17 837.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 drawout toggle vertical 3P 1 front connection on busbar 36 1087.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 fixed toggle vertical 3P 1 front connection on adaptor 19 687.5 mm
650 mm 1000 mm Prisma P cubicle Masterpact NW32 fixed toggle vertical 3P 1 rear connection on adaptor 14 437.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 fixed toggle vertical 3P 1 front connection on Canalis 28 1137.5 mm
650 mm 1000 mm Prisma P cubicle Masterpact NW32 fixed toggle vertical 3P 1 rear connection on Canalis 16 787.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 fixed toggle vertical 3P 1 front connection on busbar 36 1037.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 drawout toggle vertical 4P 1 front connection on adaptor 36 1087.5 mm
650 mm 1000 mm Prisma P cubicle Masterpact NW32 drawout toggle vertical 4P 1 rear connection on adaptor 15 487.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 drawout toggle vertical 4P 1 front connection on adaptor 20 737.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 drawout toggle vertical 4P 1 front connection on Canalis 28 1137.5 mm
650 mm 1000 mm Prisma P cubicle Masterpact NW32 drawout toggle vertical 4P 1 rear connection on Canalis 17 837.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 drawout toggle vertical 4P 1 front connection on busbar 36 1087.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 fixed toggle vertical 4P 1 front connection on adaptor 19 687.5 mm
650 mm 1000 mm Prisma P cubicle Masterpact NW32 fixed toggle vertical 4P 1 rear connection on adaptor 14 437.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 fixed toggle vertical 4P 1 front connection on Canalis 28 1137.5 mm
650 mm 1000 mm Prisma P cubicle Masterpact NW32 fixed toggle vertical 4P 1 rear connection on Canalis 16 787.5 mm
650 mm 600 mm Prisma P cubicle Masterpact NW32 fixed toggle vertical 4P 1 front connection on busbar 36 1037.5 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Mercury Free	
✓	RoHS Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Eu RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information