Product datasheet





PLAIN FRONT PLATE W300 4M

03814

! Discontinued on: 5 Apr 2023

EAN Code: 3303430038146

① Discontinued

Main

Range	Prisma	
Range Of Product	Prisma G Prisma P	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G duct Prisma Prisma P cubicle	
Type Of Front Plate	Plain	
Installed Device	TeSys: fixed TeSys U - horizontal installation Altistart: ATS01N103/106FT Phaseo: LV/LV transformer	
Poles Description	4 x 3P: modular rail support: TeSys U horizontal installation	

Complementary	
Enclosure/Cubicle Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle duct - width 400 mm depth 400 mm
Number Of Vertical Modules [50 Mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	200 mm
Width	250 mm
Net Weight	0.48 kg
Quantity Per Set	Set of 1
Functional Unit	300 mm Prisma G floor-standing duct TeSys TeSys U fixed horizontal 3P 4 direct 4 300 mm Prisma G wall-mounted duct TeSys TeSys U fixed horizontal 3P 4 direct 4 300 mm Prisma G floor-standing duct Altistart ATS01N103/106FT 19 4 300 mm Prisma G wall-mounted duct Altistart ATS01N103/106FT 19 4 300 mm Prisma G floor-standing duct Phaseo LV/LV transformer 4 300 mm Prisma G wall-mounted duct Phaseo LV/LV transformer 4

Life Is On Schneider 26 Apr 2024

400 mm 400 mm Prisma P cubicle 4



Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	21.5 cm
Package 1 Length	26.5 cm
Package 1 Weight	470.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	16.5 cm
Package 2 Width	23.0 cm
Package 2 Length	27.5 cm
Package 2 Weight	4.9 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	600
Package 3 Height	113.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	283.2 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile