Product datasheet

Specifications

, Green Premium™



(!) Discontinued

Acti9 - IH - mechanical time switch - 24 h - 150 h memory

15337	
Discontinued on: 18 Oct 2020	
() End-of-service on: 1 Mar 2023	
EAN Code: 3303430153375	

Main

Range Of Product	Acti9
Product Name	Acti9 IH
Device Short Name	IH
Product Or Component Type	Mechanical time switch
Number Of Channels	2
Function Available	Manual time changeover

Complementary

Device Application	Building
Load Type	Parallel-corrected fluorescent tube 1 x conventional ballast 58 W Non-corrected fluorescent tube 10 x conventional ballast 58 W Serial-corrected fluorescent tube 10 x conventional ballast 58 W Non-corrected fluorescent tube 15 x conventional ballast 40 W Serial-corrected fluorescent tube 15 x conventional ballast 40 W Parallel-corrected fluorescent tube 2 x conventional ballast 40 W 230 V AC halogen lamp 1100 W 230 V AC incandescent lamp 1100 W Dual mounted fluorescent tube 5 x conventional ballast 2 x 100 W Dual mounted fluorescent tube 5 x conventional ballast 2 x 58 W Non-corrected fluorescent tube 6 x conventional ballast 100 W

Cycle Duration	24 h
Maximum Number Of Switchings	24 on - 24 off
Minimum Interval Duration	30 min
Type Of Setting	Manual time changeover
Measurement Accuracy	+/- 1 s/day 20 °C
Power Consumption In Va	2.5 VA
Maximum Switching Current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] Rated Operational Voltage	230 V AC - 1510 % at 50/60 Hz
Battery Life	6 year(s)
Backup Time	150 h time and program saving
Mounting Support	DIN rail
9 Mm Pitches	6
Colour Tint	White (RAL 9003)
Connections - Terminals	Screw terminals

Width	54 mm
Height	82 mm
Depth	66 mm
Net Weight	0.216 kg

Environment

Ambient Air Temperature For Operation	-2055 °C
Ip Degree Of Protection	Terminals: IP20 B

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.8 cm
Package 1 Width	7.8 cm
Package 1 Length	10.8 cm
Package 1 Weight	230 g

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information