

Product datasheet

Specifications



voltage release - iMX - tripping unit - 12..24 VAC

Local distributor code:
396737265 A9A26478

EAN Code: 3606480087936

Main

Range Of Product	Acti9
Product Or Component Type	Shunt trip release
Device Short Name	iMX
[Uc] Control Circuit Voltage	12...24 V AC 50/60 Hz 12...24 V DC
9 Mm Pitches	2

Complementary

Range Compatibility	Acti 9 Acti9 iC65 Acti 9 Acti9 ARA Acti 9 Acti9 iDPN Vigi Acti 9 Acti9 iID Acti 9 Acti9 iSW-NA Acti 9 Acti9 RCA Acti 9 Acti9 iDPN (China version) Acti 9 Acti9 iC60 Acti 9 Acti9 iC40
Local Signalling	Action indicator
Mounting Mode	Clip-on
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	Top and bottom: YES
Width	18 mm
Colour	White
Connections - Terminals	Clamp terminal - 2 cable(s) 2.5 mm ² - flexible with cable end Clamp terminal - 1 cable(s) 6 mm ² - rigid Clamp terminal - 2 cable(s) 2.5 mm ² - rigid Clamp terminal - 1 cable(s) 4 mm ² - flexible
Tightening Torque	1 N.m
Compatibility Code	IMX

Environment

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-35...70 °C
Ambient Air Temperature For Storage	-40...85 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.9 cm
Package 1 Width	7.9 cm
Package 1 Length	9.4 cm
Package 1 Weight	76 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	8.6 cm
Package 2 Width	9.9 cm
Package 2 Length	26.7 cm
Package 2 Weight	665 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	6.472 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information