



auxiliary contact, Acti9, iOF+SD 24, 1NO + 1NC, DC

Local distributor code: 399363513

A9A26897

! Discontinued on: 24 Jul 2023

EAN Code: 3606480461613

! Discontinued

Main

Range Of Product	Acti9	
Product Or Component Type	OC and fault contact	
Device Short Name	iOF+SD 24	
Device Application	For Smartlink interface	
Signal Contacts Composition	1 NO + 1 NC	
[In] Rated Current	urrent DC-12 2100 mA at 24 V, DC +/- 20 %	
9 Mm Pitches	1	

Complementary

[Ui] Rated Insulation Voltage	500 V conforming to IEC 60664-1	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60664-1	
Local Signalling	Mechanical indicator	
Mounting Mode	Clip-on	
Mounting Support	DIN rail	
Comb Busbar And Distribution Block Compatibility	Bottom: YES	
Height	88 mm	
Width	9 mm	
Depth	73.5 mm	
Net Weight	25 g	
Colour	White	
Electrical Durability	20000 cycles conforming to IEC 60947-5-4	
Connections - Terminals	Spring-loaded terminal Ti24 (top) 2 cable(s) 0.51.5 mm² - flexible Spring-loaded terminal Ti24 (top) 2 cable(s) 0.51.5 mm² - rigid	
Wire Stripping Length	10 mm	

Environment

Standards	IEC 60947-5-4 IEC 60947-5-1
Quality Labels	CE
Pollution Degree	2 conforming to IEC 60664-1
Overvoltage Category	III

Tropicalisation	2 conforming to IEC 60947-5-1
Relative Humidity	93 % at 40 °C
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	8.0 cm
Package 1 Length	9.2 cm
Package 1 Weight	39.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.3 cm
Package 2 Width	9.8 cm
Package 2 Length	27.0 cm
Package 2 Weight	550.0 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	120
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	5.987 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information