

CANALIS FEED UNIT WHITE

Local distributor code:

395944693 KBA25ABG4W



EAN Code: 3606480498695

Main

Range Of Product	Canalis
Device Short Name	КВА
Product Compatibility	Canalis KBA busbar trunking 25 A
Offer Type	Classic Control system
Product Or Component Type	Feed unit
Conductors Material	Aluminium
[le] Rated Operational Current	25 A
[Ue] Rated Operational Voltage	230400 V
Number Of Circuits	1
Busbar Trunking Polarity	3L + N + PE L + N + PE
Protection Type	Without protection
Control Type	Communicating
Communication Port Protocol	DALI
Colour	White (RAL 9003)

Complementary

Provided Equipment	End cover
Mounting Location	Left
Mounting Mode	By screws
Mounting Support	Busbar
Connections - Terminals	Terminal block - Pg 16 - screw clamp connector for 4 mm²
Width	273 mm
Depth	57 mm
Height	57 mm
Net Weight	200 g
Standards	IEC 61439-6

Environment

Ip Degree Of Protection IP55 conforming to IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	5.5 cm
Package 1 Length	29.0 cm
Package 1 Weight	216.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	24
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5.8 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	192
Package 3 Height	75 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	54 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information Yes	
⊘	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

KBA25ABG4W

Dimension Drawings



