Product datasheet

Specifications





CENTER FEED UNIT 40A

Local distributor code: 21470114

KBA40ABT4W

EAN Code: 3606480000287

Main

Range Of Product	Canalis	
Device Short Name	КВА	
Product Compatibility	Canalis KBA busbar trunking 2540 A	
Offer Type	Classic Control system	
Product Or Component Type	Feed unit	
Conductors Material	Aluminium	
[le] Rated Operational Current	40 A 25 A	
[Ue] Rated Operational Voltage	230400 V	
Number Of Circuits	1	
Busbar Trunking Polarity	3L + N + PE L + N + PE	
Protection Type	Without protection	
Control Type	Communicating	
Communication Port Protocol	DALI	
Colour	White (RAL 9003)	

Complementary

Provided Equipment	End cover
Mounting Location	Central
Mounting Mode	By screws
Mounting Support	Busbar
Connections - Terminals	Terminal block - Pg 21 - screw clamp connector for 10 mm ²
Width	562 mm
Depth	75.5 mm
Height	75.5 mm
Net Weight	500 g
Standards	IEC 61439-6

Environment

Ip Degree Of Protection

IP55 conforming to IEC 60529

Packing Units

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	22.0 cm
Package 1 Length	64.0 cm
Package 1 Weight	2.7 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	22
Package 2 Height	80.0 cm
Package 2 Width	80.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	67.9 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Product datasheet

Dimension Drawings

