Product datasheet

Specifications



CENTER FEED UNIT 40A

Local distributor code:

23348189 KBB40ABT4W



EAN Code: 3606480001147

Main

Range Of Product	Canalis	
Device Short Name	KBB	
Product Compatibility	Canalis KBB busbar trunking 2540 A	
Offer Type	Classic	
Product Or Component Type	Feed unit	
Conductors Material	Aluminium	
[le] Rated Operational Current	40 A	
[Ue] Rated Operational Voltage	230400 V	
Number Of Circuits	1	
Busbar Trunking Polarity	3L + N + PE L + N + PE	
Protection Type	Without protection	
Control Type	Without	
Colour	White (RAL 9003)	

Complementary

Provided Equipment	End cover	
Mounting Location	Central	
Mounting Mode	By clips	
Mounting Support	Busbar	
Connections - Terminals	Terminal block - Pg 21 - screw clamp connector for 10 mm²	
Width	244 mm	
Depth	75.5 mm	
Height	75.5 mm	
Net Weight	400 g	
Standards	IEC 61439-6	

Environment

Ip Degree Of Protection IP55 conforming to IEC 60529

Packing Units

Unit Type Of Package 1 PCE

Number Of Units In Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	64.0 cm
Package 1 Length	22.0 cm
Package 1 Weight	2.95 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	22
Package 2 Height	77.0 cm
Package 2 Width	80.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	73.4 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes
Ø	Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Dimension Drawings

