Product datasheet

Specification





Canalis - tap-off unit - 10A - fixed polarity - pre-wired - L1+N+PE - green

Local distributor code: 23349366

KBC10DCS101

EAN Code: 3606480002113

Main

Range	Canalis
Offer Type	Classic Control system
Product Or Component Type	Connector
Device Application	Lighting Power socket distribution
Range Compatibility	Canalis KBA busbar trunking Canalis KBB busbar trunking
[le] Rated Operational Current	10 A at 35 °C
[Ue] Rated Operational Voltage	230240 V
Network Frequency	50/60 Hz
Communication Port Protocol	DALI
Tap-Off Unit Polarity	L1 + N + PE
Tap-Off Unit Connector Type	With fixed polarity
Tap-Off Lock Colour	Green

Complementary

Colour	Cream (RAL 9001)
[Uimp] Rated Impulse Withstand Voltage	4 kV
[Ui] Rated Insulation Voltage	690 V
Protection Type	Without protection
Electrical Connection	Pre-wired with SO5Z1Z1-F - 3 x 1.5 mm² for 0.8 m long
Width	55 mm
Depth	12.5 mm
Height	42 mm
Net Weight	100 g
Quantity Per Set	Set of 10
Standards	EN/IEC 61439-1 EN/IEC 61439-6

Environment

Ip Degree Of Protection IP55 conforming to EN/IEC 60529

Packing Units



Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.300 cm
Package 1 Width	4.000 cm
Package 1 Length	6.000 cm
Package 1 Weight	66.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	10.000 cm
Package 2 Width	14.500 cm
Package 2 Length	39.000 cm
Package 2 Weight	764.000 g
Unit Type Of Package 3	P12
Number Of Units In Package 3	960
Package 3 Height	74.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	97.776 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >






Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc





Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Product datasheet

KBC10DCS101

Dimension Drawings