



TeSys D - contactor coil - LXD1 - 400 V AC 50/60 Hz for 9... 38 A contactor

Local distributor code: 381809292

LXD1V7

EAN Code: 3389110467963

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LXD1
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	400 V AC 50/60 Hz
Average Resistance	1633 Ohm at 20 °C
Inductance Of Closed Circuit	60 H
Product Compatibility	CAD LC1DT20DT40 LC1D09D38
Mechanical Durability	15 Mcycles
Maximum Operating Rate	3600 cyc/h 60 °C

Complementary

Coil Technology	Without built-in suppressor module	
Control Circuit Voltage Limits	Drop-out: 0.30.6 Uc at 50/60 Hz (at <60 °C)	
	Operational: 0.81.1 Uc at 50 Hz (at <60 °C)	
	Operational: 0.851.1 Uc at 60 Hz (at <60 °C)	
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 20 °C)	
	70 VA 50 Hz cos phi 0.75 (at 20 °C)	
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 20 °C)	
	7 VA 50 Hz cos phi 0.3 (at 20 °C)	
Heat Dissipation	23 W at 50/60 Hz	

Environment

Ambient Air Temperature For Operation	-560 °C
Net Weight	0.07 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	6.200 cm
Package 1 Length	4.000 cm
Package 1 Weight	72.000 g

Unit Type Of Package 2	S02
Number Of Units In Package 2	100
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.446 ka

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information