



FEED UNIT 40A RIGHT **MOUNTING**

Local distributor code: 385364225

KBA40ABD4TW

EAN Code: 3606480000218

Main

Range Of Product	Canalis	
Device Short Name	КВА	
Product Compatibility	Canalis KBA busbar trunking 2540 A	
Offer Type	Control system	
Product Or Component Type	Feed unit	
Conductors Material	Aluminium	
[le] Rated Operational Current	40 A 25 A	
[Ue] Rated Operational Voltage	230400 V	
Number Of Circuits	1	
Busbar Trunking Polarity	ing Polarity 3L + N + PE L + N + PE	
Protection Type	Without protection	
Control Type	Communicating	
Communication Port Protocol	DALI KNX	
Colour	White (RAL 9003)	

Complementary

Provided Equipment	End cover	
Mounting Location	Right	
Mounting Mode	By screws	
Mounting Support	Busbar	
Connections - Terminals	Terminal block - Pg 21 - screw clamp connector for 10 mm²	
Width	320 mm	
Depth	75.5 mm	
Height	78.5 mm	
Net Weight	500 g	
Standards	IEC 61439-6	

Environment

Ip Degree Of Protection IP55 conforming to IEC 60529

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7.5 cm
Package 1 Length	39 cm
Package 1 Weight	800 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	20 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	8.4 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	64
Package 3 Height	50 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	75.7 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc
9	Toxic Heavy Metal Free
②	Mercury Free
Ø	Rohs Exemption Information Yes
⊘	Pvc Free
⊘	Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations