Product datasheet

Specifications





FEED UNIT 40A LEFT MOUNTING

Local distributor code: 385364403

KBB40ABG44TW

EAN Code: 3606480001055

Main

Range Of Product	Canalis
Device Short Name	КВВ
Product Compatibility	Canalis KBB busbar trunking 2540 A
Offer Type	Control system
Product Or Component Type	Feed unit
Conductors Material	Aluminium
[le] Rated Operational Current	40 A 25 A
[Ue] Rated Operational Voltage	230400 V
Number Of Circuits	2
Busbar Trunking Polarity	3L + N + PE L + N + PE
Protection Type	Without protection
Control Type	Communicating
Communication Port Protocol	DALI KNX
Colour	White (RAL 9003)

Complementary

Provided Equipment	End cover
Mounting Location	Left
Mounting Mode	By clips
Mounting Support	Busbar
Connections - Terminals	Terminal block - Pg 21 - screw clamp connector for 610 mm ²
Width	244 mm
Depth	103.5 mm
Height	75.5 mm
Net Weight	400 g
Standards	IEC 61439-6

Environment

Ip Degree Of Protection

IP55 conforming to IEC 60529

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	11.000 cm
Package 1 Length	27.000 cm
Package 1 Weight	700.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.841 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations