

# Product datasheet

Specifications



## Spacial SF external fixing side panels - 1400x800 mm

Local distributor code:

392984106

NSY2SP148

**Discontinued on:** 9 Feb 2023

**EAN Code:** 3606485119847

**Discontinued**

### Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Side panel
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Sides of enclosure
Quantity Per Set	Set of 1

### Complementary

Range Compatibility	Spacial Spacial SF
Device Composition	fixing elements 2 side panel
Material	Steel
Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By screws - screw type captive - from the outside of enclosure location
Height	Nominal: 1400 mm
Width	Nominal: 800 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	77.5 cm
Package 1 Length	140.0 cm
Package 1 Weight	25.56 kg
Unit Type Of Package 2	P2M
Number Of Units In Package 2	12
Package 2 Height	89.0 cm
Package 2 Width	200.0 cm
Package 2 Length	120.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	404.0 kg
------------------	----------

## Logistical informations

Country Of Origin	ES
-------------------	----

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Mercury Free

 RoHS Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations