# **Product datasheet**

Specifications





# ClimaSys PTC heating resistance 100W, 12-24V

Local distributor code: 385509789

NSYCR100WU1

EAN Code: 3606480152184

#### Main

| Range                     | ClimaSys          |
|---------------------------|-------------------|
| Product Name              | ClimaSys CR       |
| Product Or Component Type | Resistance heater |
| Power Range               | 90 W              |
| Input Voltage             | 1224 V DC         |

#### Complementary

| · · · · · · · · · · · · · · · · J        |  |
|--|--|
| Operating Position                       | Vertical   |
| Ambient Air Temperature For<br>Operation | -4070 °C   |
| Ip Degree Of Protection                  | IP20   |
| Product Certifications                   | VDE<br>UL  |
| Material                                 | Body: extruded aluminium   |
| Condition Of Use                         | Heaters must be installed with a thermal controller<br>Electrical protection is needed<br>Air sealed enclosure |
| Fixing Mode                              | By clips   |
| Mounting Support                         | 35 mm DIN rail   |

### **Packing Units**

| -                            |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 6 cm     |
| Package 1 Width              | 8 cm     |
| Package 1 Length             | 19.5 cm  |
| Package 1 Weight             | 476 g    |
| Unit Type Of Package 2       | PAL      |
| Number Of Units In Package 2 | 16       |
| Package 2 Height             | 20 cm    |
| Package 2 Width              | 40 cm    |
| Package 2 Length             | 60 cm    |
| Package 2 Weight             | 7.616 kg |
|                              |          |

# **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Compliant with Exemptions   |
| China Rohs Regulation    | China RoHS declaration<br>Product out of China RoHS scope. Substance declaration for your information                       |
| Environmental Disclosure | Product Environmental Profile   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | No need of specific recycling operations  |