## **Product datasheet**

Specifications





# ClimaSys PTC heating resistance 10W, 110-250V Local distributor code:

22130563

NSYCR10WU2

EAN Code: 3606480152115

#### Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Resistance heater
Power Range	10 W
Input Voltage	110250 V AC 50/60 Hz
Electrical Connection	Cable 2 x 0.75 mm² length: 300 mm

### Complementary

Operating Position	Vertical
Ambient Air Temperature For Operation	-4070 °C
Ip Degree Of Protection	IP20
Product Certifications	UL VDE
Material	Body: extruded aluminium
Height	External: 85 mm
Width	External: 25 mm
Depth	External : 57 mm
Condition Of Use	Heaters must be installed with a thermal controller Electrical protection is needed Air sealed enclosure
Fixing Mode	By clips
Mounting Support	35 mm DIN rail

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	7.500 cm
Package 1 Length	8.000 cm
Package 1 Weight	126.000 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	105
Package 2 Height	30 cm

Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	13.880 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	420
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	67.520 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations