Product datasheet

Specifications

Green Premium[™]



ClimaSys standard cooling unit side of enclosure - 640W at 230 V

Local distributor code: 402655037

NSYCU600

Discontinued on: 23 Nov 2023
End-of-service on: 23 Feb 2024

EAN Code: 3606480620782

Overview

Lead Time

Usually Ships within 4 Weeks

Main

Range	ClimaSys	
Product Name	CU	
Product Or Component Type	Cooling unit	
Mounting Type	Side	
Installation	Indoor side	
Product Destination	For enclosure	
Mounting Mode	By screws	
Supply Voltage	230 V AC at 50/60 Hz, 1 phase	
Rated Power	640 W	
Cooling Power	640 W 50/60 Hz L35-L35 470 W 50/60 Hz L35-L50	

Complementary

606 mm
316 mm
212 mm
2.1 A
8.1 A
400 W at 50/60 Hz, L35-L35 470 W at 50/60 Hz, L35-L50
1.6
Electronic controller
2055 °C at 50 Hz 2050 °C at 60 Hz
2046 °C inside the enclosure: 55 °C maximum: 2055 °C at 50 Hz outside the enclosure: 2050 °C at 60 Hz outside the enclosure:
65 dB conforming to EN/ISO 3746
25 bar

Flow Rate	Internal circuit: 330 m3/h at 50/60 Hz External circuit: 570 m3/h at 50/60 Hz
Net Weight	21 kg
Cooling Gas Type	R134a (0.23 kg)
Type Of Filter	Optional external circuit filter
Protection Type	Thermal protection: T 6 A Short-circuit protection (magnetic):
Material	Steel
Colour	Grey (RAL 7035)

Environment

Product Certifications	CE
Directives	2006/95/EC - low voltage directive 2006/42/EC - machinery
	2004/108/EC - electromagnetic compatibility
Standards	EN 60335-1
	EN 378
	EN/ISO 12100
	EN 60204-1
	EN 60335-2-40
Ip Degree Of Protection	IP54 conforming to IEC 60529 (on the internal circuit) IP34 conforming to IEC 60529 (on the external circuit)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.2 cm
Package 1 Width	31.6 cm
Package 1 Length	60.6 cm
Package 1 Weight	21.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	6
Package 2 Height	84.5 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	167.0 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information