

Product datasheet

Specifications



Climasys forced vent. 54 m3/h, 230V, 2 metal grilles and 2 anti-insect filters

Local distributor code:
385511007

NSYCVF54M230MM2

EAN Code: 3606480151415

Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan
Type Of Filter	Anti-insect
Flow Rate	Free flow rate without filter or grille: 170 m3/h Overall flow rate: 54 m3/h at 50 Hz
Input Voltage	230 V 50/60 Hz

Complementary

Height	External: 120 mm
Width	External: 120 mm
Depth	External : 38 mm
Cut-Out Dimensions	96 x 96 mm
Material	Outlet grille: steel Filter: stainless steel 304L
Colour	Outlet grille: grey (RAL 7035)
Ip Degree Of Protection	IP33
Device Composition	1 axial motor 1 power cord 2 anti-insect filter 2 metal louver

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	15.0 cm
Package 1 Length	17.0 cm
Package 1 Weight	967.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	20.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	10.93 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	300
Package 3 Height	80.0 cm
Package 3 Width	100.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	350.9 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information