


# Product datasheet

Specifications



## Plain left door Spacial CRNG H1400xW500 RAL 7035

NSYDCRNG145L

 **Discontinued on:** 9 Feb 2023

**EAN Code:** 3606480491603

 **Discontinued**

### Main

|                                    |                          |
|------------------------------------|--------------------------|
| Range                              | Spacial                  |
| Accessory / Separate Part Category | Enclosure accessory      |
| Product Or Component Type          | Left door                |
| Application                        | Multi-purpose            |
| For Enclosure Nominal Dimensions   | -                        |
| Mounting Location                  | Front                    |
| Range Compatibility                | Spacial Spacial CRN      |
| Device Composition                 | 1 door<br>locking system |
| Quantity Per Set                   | Set of 1                 |

### Complementary

|                   |                                   |
|-------------------|-----------------------------------|
| Material          | Door: sheet steel                 |
| Colour            | Grey (RAL 7035)                   |
| Surface Finish    | Textured epoxy polyester          |
| Lock Type         | Lock 5 mm double bar              |
| Number Of Locks   | 1                                 |
| Door Type         | Plain                             |
| Door Opening Side | Reversible (120 °)                |
| Maximum Load      | 50 kg/m²                          |
| Height            | Nominal: 1400 mm<br>Real: 1420 mm |
| Width             | Nominal: 500 mm                   |
| Net Weight        | 14.31 kg                          |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 5.0 cm   |
| Package 1 Width              | 51.0 cm  |
| Package 1 Length             | 142.0 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |          |
|------------------------------|----------|
| Package 1 Weight             | 14.31 kg |
| Unit Type Of Package 2       | P2M      |
| Number Of Units In Package 2 | 20       |
| Package 2 Height             | 73.0 cm  |
| Package 2 Width              | 200.0 cm |
| Package 2 Length             | 120.0 cm |
| Package 2 Weight             | 332.8 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information