



# Plain mounting plate H300xW250mm made of galvanised sheet steel

Local distributor code: 392865393 NSYMM3025

EAN Code: 3606480183270

#### Main

| Range                                 | Spacial   |  |
|---------------------------------------|---|--|
| Accessory / Separate Part<br>Category | Mounting accessory  |  |
| Product Or Component Type             | Mounting plate  |  |
| Device Application                    | Multi-purpose   |  |
| <b>Enclosure Nominal Dimensions</b>   | - H: 300 mm W: 250 mm   |  |
| Mounting Location                     | Step slide<br>Direct fixing on backstuds                          |  |
| Mounting Plate Description            | Plain   |  |
| Range Compatibility                   | Spacial Spacial S3D<br>Spacial Spacial CRN<br>Spacial Spacial S3X |  |
| Quantity Per Set                      | Set of 1  |  |
| Material                              | Galvanised steel  |  |

# Complementary

| Fixing Mode                | Screwed on backstuds - screw type M8 By fixing element |
|----------------------------|--|
| Permanent Permissible Load | 60 kg  |
| Height                     | 250 mm   |
| Width                      | 200 mm   |
| Thickness                  | 1.8 mm   |
| Net Weight                 | 0.706 kg   |

## **Packing Units**

| Unit Type Of Package 1       | PCE     |
|------------------------------|---------|
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 1.0 cm  |
| Package 1 Width              | 20.0 cm |
| Package 1 Length             | 25.0 cm |
| Package 1 Weight             | 792.0 g |

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

| <b>⊘</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>9</b> | Toxic Heavy Metal Free     |     |
| <b>②</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration            |
| China Rohs Regulation    | China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |