



ClimaSys PTC heating resistance 10W,110-250V insulate

Local distributor code: 388825826

88825826 NSYCR10WU2C

EAN Code: 3606480152252

Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Resistance heater
Power Range	10 W
Input Voltage	110250 V AC 50/60 Hz
Electrical Connection	2 screw terminals 2.5 mm ²

Complementary

Operating Position	Vertical	
Ambient Air Temperature For Operation	-4070 °C	
Ip Degree Of Protection	IP20	
Electrical Insulation Class	Class II	
Product Certifications	VDE UL	
Material	Body: extruded aluminium Cover: plastic	
Height	External: 98 mm	
Width	External: 38 mm	
Depth	External : 75 mm	
Condition Of Use	Electrical protection is needed Air sealed enclosure Heaters must be installed with a thermal controller	
Fixing Mode	By clips	
Mounting Support	35 mm DIN rail	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8.0 cm
Package 1 Length	11.0 cm
Package 1 Weight	160.0 g
Unit Type Of Package 2	CAR

Number Of Units In Package 2	50
Package 2 Height	19.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	9.46 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	500
Package 3 Height	51.0 cm
Package 3 Width	100.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	114.6 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations