
Product datasheet

Specification





Insulating mounting plate for enclosure H700xW500mm made of polyester

Local distributor code: 398249340

NSYMPP75

EAN Code: 3606480183515

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	-	
Mounting Location	Step slide Direct fixing on backstuds	
Mounting Plate Description	Plain	
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	Per Set Set of 1	
Material	Fibreglass reinforced polyester	
Colour	Grey (RAL 7035)	

Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element
Permanent Permissible Load	875 kg
Height	Nominal: 665 mm Enclosure nominal dimension: 700 mm
Width	Nominal: 450 mm Enclosure nominal dimension: 500 mm
Thickness	4 mm
Net Weight	2.1 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.4 cm
Package 1 Width	45.0 cm
Package 1 Length	66.5 cm
Package 1 Weight	2.155 kg
Unit Type Of Package 2	PAL

Number Of Units In Package 2	100
Package 2 Height	100.0 cm
Package 2 Width	120.0 cm
Package 2 Length	100.0 cm
Package 2 Weight	231.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations