
Product datasheet

Specifications





Insulating mounting plate for enclosure H800xW600mm made of polyester

Local distributor code: 398249353

NSYMPP86

EAN Code: 3606480183522

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Location	Step slide Direct fixing on backstuds
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	Fibreglass reinforced polyester
Colour	Grey (RAL 7035)

Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element
Permanent Permissible Load	63.1 kg S3D, CRN, S3X enclosures 63.1 kg PLM enclosure
Maximum Load	150 kg PLM enclosure 150 kg S3D, CRN, S3X enclosures
Height	765 mm nominal: 800 mm enclosure nominal dimension:
Width	550 mm nominal: 600 mm enclosure nominal dimension:
Surface And Useful Surface	42.1 dm²
Thickness	5 mm
Net Weight	3.8 kg
Variant Particularity	With enclosures H800 x W1200

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.5 cm

4 May 2024 Life Is On Schneider

Package 1 Width	55.0 cm	
Package 1 Length	76.5 cm	
Package 1 Weight	3 787 kg	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
Ø	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations